


X09701

Dust extractor DUSTOMAT DRY 2700







Drawings may deviate

Technical data (Technical data may vary)

| Mains voltage | 400 V | Main filter surface | 2 x 5m ² |
|------------------------|------------|--|------------------------|
| Nominal power | 3,0 kW | Main filter quantity | 2 Pieces |
| Mains frequency | 50 Hz | Collection volume | 50 L |
| Nominal current | 6 A | Dimensions (L x W x H) | 1.630 x 840 x 1.430 mm |
| Circuit breaker | C16A | Weight | 300 kg |
| Max. volume flow | 2.700 m³/h | Type of cleaning | Manual rotation |
| Max. negative pressure | 2.900 Pa | Compressed air consumption at 4bar with valve opening time 0.12sec | 50l / Impuls |
| Sound pressure level | [dBA] 68 | Compressed air connection 1x for automatic / 2x for manual | 3/4" |
| Intake opening | Ø 180 mm | | |

Application range

» For the single or multi-station extraction

 » For dry, free-flowing dusts as well as for chips (depending on the version, also for carcinogenic, flammable or explosive media)

Configuration example

- » Mobile version
- » Air recirculation operation
- » Collection volume: 50 L
- » Filter type cartridge: PE, antistatic
- » Without Precoating
- » Housing material: Steel (S235JR)
- » Material of parts in contact with the medium: Steel (S235JR)

Special Features

- » Particularly long filter life due to optimum ratio between air volume flow and filter surface as well as very effective filter cleaning.
- » High suction power ensures optimum extraction results at your collection point
- » Filter cleaning that is gentle on operating resources, thanks to the latest cleaning technologies and intelligent cleaning control based on demand
- » High separation efficiency of the filter media used ensures compliance with the required standards/directives.
- » The sound-insulated housing design and targeted air routing ensure low operating noise for quiet (continuous) operation.
- » Detachable/mobile dust collection container with large capacity ensures simple and quick removal or disposal of the separated material and reduces the number of disposal cycles. This minimises maintenance efforts as well as downtimes in the production process.

State of the art: This document was generated automatically. Technical changes reserved!